

## TLI4971-A120T5-U-E0001

Reference: Data Sheet Rev.1.0

Affected samples:

Date code: 1944

Sample lot numbers: ML922475G20, ML922475G21, ML922475G24, ML922475G25

### Overview

This document lists the errata of the TLI4971-A120T5-U-in relation to the Data Sheet Rev.1.0.

### Pre-Configured Fast Over-Current Detection Threshold Levels

The threshold level of the OCD1 and OCD2 fast over-current detection pins is different to the pre-set standard product configuration mentioned in the Data Sheet Rev.1.0.

Table 1 shows the actual programmed OCD1 threshold value.

**Table 1 Pre-configured threshold level, OCD1**

Parameter	Actual pre-configured product setting	Note / Test Conditions
Threshold level	2.7	Factor with respect to FS (Full Scale)

Table 2 shows the actual programmed OCD2 threshold value.

**Table 2 Pre-configured threshold level, OCD2**

Parameter	Actual pre-configured product setting	Note / Test Conditions
Threshold level	1.39	Factor with respect to FS (Full Scale)

Note:

The OCD threshold levels can be reprogrammed by the user according to the values listed in the data sheet table 6 and table 7.